

## 3-Point Internal Micrometer

### Holtest Set

Item number: 368-914

#### Images



#### Description

This is a set of three-point and two-point internal micrometers that offers you the following benefits:

- Complete unit set.
- Carbide measuring surface (2-6 mm range).
- Titanium-coated measuring pins (>6 mm range) give you excellent durability and impact resistance.
- Delivered with setting rings and extension rod (>6 mm range).

#### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	50 - 100 mm
<b>Graduation:</b>	0,005 mm
<b>Individual ranges:</b>	50-63, 62-75, 75-88, 87-100 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
<b>Measuring spindle:</b>	Spindle pitch 0,5 mm
<b>Measuring face:</b>	Titanium coated tungsten carbide taper: tungsten carbide

<b>Measuring method:</b>	3-point
--------------------------	---------

<b>Models included:</b>	368-170 / 368-171 / 368-172 / 368-173
-------------------------	---------------------------------------

<b>Setting rings included:</b>	ø62 mm (177-314) ø87 mm (177-318)
--------------------------------	--------------------------------------

<b>Delivered:</b>	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
-------------------	---

<b>Mass:</b>	2030 g
--------------	--------