

3-Point Internal Micrometer

Holtest Set

Item number: 368-926

Images



Description

This is a set of three-point and two-point internal micrometers that offers you the following benefits:

- Complete unit set.
- Carbide measuring surface (2-6 mm range).
- Titanium-coated measuring pins (>6 mm range) give you excellent durability and impact resistance.
- Delivered with setting rings and extension rod (>6 mm range).

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	0,08 - 0,12 "
Graduation:	≤ 0.5": 0.0001", >0.5": 0.0002"
Individual ranges:	0.08-0.1", 0.1-0.12"
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : ø 17 mm Over 12 mm : ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Tungsten carbide
Measuring method:	2-point
Models included:	368-21 / 368-22
Setting rings included:	ø0.1" (177-209)
Delivered:	Including box, hex wrench, certificate of inspection, setting ring (1 pcs.)

Mass:

310 g