

## 3-Point Internal Micrometer

### Holtest Set

Item number: 368-927

#### Images



#### Description

This is a set of three-point and two-point internal micrometers that offers you the following benefits:

- Complete unit set.
- Carbide measuring surface (2-6 mm range).
- Titanium-coated measuring pins (>6 mm range) give you excellent durability and impact resistance.
- Delivered with setting rings and extension rod (>6 mm range).

#### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0,12 - 0,28 "
<b>Graduation:</b>	≤ 0.5": 0.0001", >0.5": 0.0002"
<b>Individual ranges:</b>	0.12-0.16", 0.16-0.2", 0.2-0.24", 0.24-0.28"
<b>Scale:</b>	Thimble and sleeve satin chrome finish, Up to 12 mm : ø 17 mm Over 12 mm : ø 23 mm
<b>Measuring spindle:</b>	Spindle pitch 0,635 mm
<b>Measuring face:</b>	Tungsten carbide
<b>Measuring method:</b>	2-point
<b>Models included:</b>	368-23 / 368-24 / 368-25
<b>Setting rings included:</b>	ø0.16 " (177-206) ø0.24" (177-207)
<b>Delivered:</b>	Including box, hex wrench, certificate of inspection, setting rings (2 pcs.)

**Mass:**

505 g