

3-Point Internal Micrometer

Holtest Set

Item number: 368-991

Images



Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	12 - 20 mm
Graduation:	0,005 mm
Individual ranges:	12-16, 16-20 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-764 / 368-765
Setting rings included:	Ø16 mm (177-177)

Delivered:

Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting ring (1 pcs.), extension rod

Mass:

310 g

Accessories**Optional accessories:****Holtest, Borematic Extension
150mm**

for 12-20mm Measuring Range
Art No. 952621
Suggested retail price: 118.00 €*

**Holtest, Borematic Extension
150mm**

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 128.00 €*

**Holtest, Borematic Extension
150mm**

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: 222.00 €*
