

3-Point Internal Micrometer

Holtest Set

Item number: 368-992

Images



Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

Features

Model:	HT2-50RST
Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	20 - 50 mm
Graduation:	0,005 mm
Individual ranges:	20-25, 25-30, 30-40, 40-50 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-766 / 368-767 368-768 / 368-769
Setting rings included:	Ø25 mm (177-139) Ø40 mm (177-290)

Delivered:

Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod

Mass:

1160 g

Accessories**Optional accessories:****Holtest, Borematic Extension
150mm**

for 12-20mm Measuring Range
Art No. 952621
Suggested retail price: 118.00 €*

**Holtest, Borematic Extension
150mm**

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 128.00 €*

**Holtest, Borematic Extension
150mm**

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: 222.00 €*