

3-Point Internal Micrometer

Holtest Set

Item number: 368-993

Images



Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

Features

Model:	HT2-100RST
Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	50 - 100 mm
Graduation:	0,005 mm
Individual ranges:	50-63, 62-75, 75-88, 87-100 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-770 / 368-771 / 368-772 / 368-773
Setting rings included:	ø62 mm (177-314) ø87 mm (177-318)

Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
Mass:	2020 g

Accessories

Optional accessories:



**Holtest, Borematic Extension
150mm**

for 12-20mm Measuring Range
Art No. 952621
Suggested retail price: **118.00 €***



**Holtest, Borematic Extension
150mm**

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: **128.00 €***



**Holtest, Borematic Extension
150mm**

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: **222.00 €***