

3-Point Internal Micrometer

Holtest Set

Item number: 368-994

Images



Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

Features

Model:	HT2-200RST
Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	100 - 200 mm
Graduation:	0,005 mm
Individual ranges:	100-125, 125-150, 150-175, 175-200 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm

Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-774 / 368-775 / 368-776 / 368-777
Setting rings included:	ø125 mm (177-298) ø175 mm (177-302)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
Mass:	4630 g

Accessories

Optional accessories:



Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: 118.00 €*



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range

Art No. 952622

Suggested retail price: 128.00 €*



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: 222.00 €*