

## 3-Point Internal Micrometer

### Holtest Set

Item number: 368-995

#### Images



#### Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

#### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0,5 - 0,8 "
<b>Graduation:</b>	≤ 0.5": 0.0001", >0.5": 0.0002"
<b>Individual ranges:</b>	0.5-0.65" , 0.65-0.8"
<b>Scale:</b>	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
<b>Measuring spindle:</b>	Spindle pitch 0,635 mm
<b>Measuring face:</b>	Hardened steel taper: hardened steel
<b>Measuring method:</b>	3-point
<b>Models included:</b>	368-864 / 368-865
<b>Setting rings included:</b>	ø0.65" (177-182)

**Delivered:**

Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting ring (1 pcs.), extension rod

**Mass:**

260 g

**Accessories****Optional accessories:****Holtest, Borematic Extension  
150mm**

for 12-20mm Measuring Range  
Art No. 952621  
Suggested retail price: 118.00 €\*

**Holtest, Borematic Extension  
150mm**

for 20-50mm Measuring Range  
Art No. 952622  
Suggested retail price: 128.00 €\*

**Holtest, Borematic Extension  
150mm**

for 50-300mm Measuring Range  
Art No. 952623  
Suggested retail price: 222.00 €\*