

Digital/Analog:	Analog
Range:	0,8 - 2 "
Graduation:	≤ 0.5": 0.0001" , >0.5": 0.0002"
Individual ranges:	0.8-1" , 1-1.2" , 1.2-1.6" , 1.6-2"
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-866 / 368-867 / 368-868 / 368-869
Setting rings included:	ø1" (177-184) ø1.6" (177-291)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
Mass:	960 g

Accessories

Optional accessories:



Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range
Art No. 952621
Suggested retail price: 120.00 €*



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 136.00 €*



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: 216.00 €*
