

3-Point Internal Micrometer

Holtest Set

Item number: 368-998

Images



Description

A Mitutoyo internal micrometer set consisting of individual gauges, the appropriate setting rings and an extension tube for depth measurement applications. Contact surfaces made of hardened steel. A ratchet guarantees repeatable measurement.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	4 - 8 "
Graduation:	≤ 0.5": 0.0001", >0.5": 0.0002"
Individual ranges:	4-5" , 5-6" , 6-7" , 7-8"
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Hardened steel taper: hardened steel
Measuring method:	3-point
Models included:	368-874 / 368-875 / 368-876 / 368-877
Setting rings included:	ø5" (177-299) ø7" (177-303)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod

Mass:

4630 g

Accessories

Optional accessories:



Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: 120.00 €*



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range

Art No. 952622

Suggested retail price: 136.00 €*



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: 216.00 €*