

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 3802AB-10

Images



Description

This is a standard, inch dial indicator. It offers you the following benefits:

- Large-diameter dial face $\varnothing = 78$ mm for easy reading
- Supplied with limit markers and a bezel clamp as standard
- 0.001" / 0.0001" graduation

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,025 "
Range per rev.:	0.01"
Dial reading:	0-10
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0.0001"
H MPE (Hysteresis):	0,0001"
R MPE (Repeatability):	$\pm 0,00003$ "
MPE first one revolution:	$\pm 0,0001$ "
MPE first 2 1/2 revolutions:	$\pm 0,0001$ "
Type:	ANSI/AGD Standard
Measuring force:	0,4-2 N
Stem:	9.52 mm / 0.375"


Contact point: Carbide tipped, thread: 4-48UNF

Continuous dial: Yes

Shockproof: Yes

Mass: 245 g

Dimensions



A: 2.41 inch

B: 2.35 inch

C: 3.07 inch

D: 0.7 inch

E: 3/4 inch

F: 0.5 inch

G: 0.32 inch

H: 2.8 inch

I: 0.35 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator Serie 2/3/4

Art No. 21EZA198

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*