Digital 3-Point Internal Micrometer

Item number: 468-177

Images

Description

These are three-point internal micrometers that offer you the following benefits:

- Individual micrometer.
- Titanium-coated measuring pins give you excellent durability and impact resistance.
- They also have excellent resistance against water and dust (IP65 protection level), allowing you to use this product in machining situations that include splashing coolant fluid.
- Large LCD display with character height of 7,5 mm enables you to read measurements easily.

- Without setting rings or extensions.

Features

Model:	HTD-200R
Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	175 - 200 mm
Digital step:	0,001 mm
Max. Permissible Error J MPE:	±5 µm
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium-coated hardened steel taper: tungsten carbide
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection
Data output:	Yes
Mass:	1210 g

Dimensions



Accessories

Optional accessories:

Promotion!

Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €***

~~Suggested retail price: **70.00 €***~~

Setting Ring 175mm

Steel
Art No. 177-302
Suggested retail price: **1,235.00 €***

Promotion!

Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type
Art No. 02AZD790B
Promo price: 72.90 €*
~~Suggested retail price: **110.00 €***~~

Promotion!

USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
Art No. 06AFM380B
Promo price: 109.00 €*
~~Suggested retail price: **141.00 €***~~

Digimatic Cable with Data Button IP Type

1m, Micrometer Type
Art No. 05CZA662
Suggested retail price: **105.00 €***

Digimatic Cable with Data Button IP Type

2m, Micrometer Type
Art No. 05CZA663
Suggested retail price: **107.00 €***

Holder for Micrometer Stand

for Series 468
Art No. 04AZB157
Suggested retail price: **62.00 €***

Holtest, Boremetic Extension 150mm

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: **222.00 €***

Promotion!

U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Promo price: **129.00 €***
~~Suggested retail price: **187.00 €***~~

Promotion!

U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Promo price: **129.00 €***
~~Suggested retail price: **187.00 €***~~

Promotion!



USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)
Art No. 06AGR543
Promo price: **259.00 €***
~~Suggested retail price: **340.00 €***~~

Spare parts

Consumable spares:

Battery SR44 1,5 V

Art No. 938882
Suggested retail price: **10.00 €***