

## Digital 3-Point Internal Micrometer

Item number: 468-263

### Images



Dust- and  
Waterproof  
IP65

www.tuv.com  
ID 0000021605



### Description

A water-resistant Mitutoyo bore gauge comprising a digital/analogue display unit and measuring head. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output. A ratchet stop guarantees repeatable measurement.


### Features

Inch-Metric:

Inch/Metric

<b>Digital/Analog:</b>	Digital
<b>Range:</b>	0,425-0,5" "
<b>Digital step:</b>	0.00005"
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 1.2 years
<b>Display:</b>	LCD, character height 7.5 mm
<b>Measuring face:</b>	Titanium-coated tungsten carbide taper: tungsten carbide
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Function lock:</b>	Yes
<b>HOLD:</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>Delivered:</b>	Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection
<b>Data output:</b>	Yes
<b>Mass:</b>	370 g

#### Dimensions



**L1:** 175 - 177 mm

**L2:** 59 mm

#### Accessories

Optional accessories:

Promotion!



**Micrometer Stand, Adjustable Angle Type**

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

Promo price: **56.00 €\***

~~Suggested retail price: 70.00 €\*~~

Promotion!



## Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **76.00 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



## USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **111.00 €\***

Suggested retail price: ~~141.00 €\*~~



## Digimatic Cable with Data Button IP Type

1 m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €\*



## Digimatic Cable with Data Button IP Type

2 m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €\*



## Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: 62.00 €\*

## Holtest, Borematic Extension 100mm



for 6-12mm Measuring Range  
Art No. 952322  
Suggested retail price: 128.00 €\*  
Mitutoyo 952322



## Setting Ring 0,425"

Steel  
Art No. 177-283  
Suggested retail price: 121.00 €\*  
42502"  
Mitutoyo  
Setting Ring  
NO.177-283  
080127  
JAPAN

Promotion!



## U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: **129.00 €\***   
Suggested retail price: ~~187.00 €\*~~

Promotion!



## U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: **129.00 €\***   
Suggested retail price: ~~187.00 €\*~~

Promotion!

Mitutoyo

**MiCAT**  
the standard in world  
metrology software  
**MeasurLink**

## USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)  
Art No. 06AGR543  
Promo price: **268.00 €\***   
Suggested retail price: ~~340.00 €\*~~

USB-ITPAK

Consumable spares:

---



**Battery SR44 1,5 V**

Art No. 938882

Suggested retail price: 7.00 €\*  

---