

Digital 3-Point Internal Micrometer

Item number: 468-269

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 000021605




Description

A water-resistant Mitutoyo bore gauge comprising a digital/analogue display unit and measuring head. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output. A ratchet stop guarantees repeatable measurement.

Features

| | |
|--|--|
| Digital/Analog: | Digital |
| Inch-Metric: | Inch/Metric |
| Range: | 1,6-2" " |
| Digital step: | 0.00005" |
| Display: | LCD, character height 7.5 mm |
| Measuring face: | Titanium-coated hardened steel taper: tungsten carbide |
| Power supply: | 1 battery SR-44 |
| Battery life: | Approx. 1.2 years |
| ABS / INC (INC ZERO): | Yes |
| Auto Power OFF after 20 min. non use: | Yes |
| Low voltage alarm: | Yes |
| Function lock: | Yes |
| HOLD: | Yes |
| 2 x PRESET: | Yes |
| Delivered: | Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection |
| Data output: | Yes |
| Mass: | 500 g |

Dimensions



L1: 214.7 - 224.7 mm

L2: 103.8 mm

Accessories

Optional accessories:

Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10

Promo price: 55.90 €*
Suggested retail price: 70.00 €*

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **72.90 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **109.00 €***

Suggested retail price: ~~141.00 €*~~



Digimatic Cable with Data Button IP Type

1m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €*



Digimatic Cable with Data Button IP Type

2m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €*



Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: 62.00 €*



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 128.00 €*
~~128.00 €~~



Setting Ring 1,6"

Steel
Art No. 177-291
Suggested retail price: 203.00 €*
~~203.00 €~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Promo price: **129.00 €*
~~187.00 €~~**

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Promo price: **129.00 €*
~~187.00 €~~**

Promotion!

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)
Art No. 06AGR543
Promo price: **259.00 €*
~~340.00 €~~**

USB-ITPAK

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 10.00 €*
