

Digital 3-Point Internal Micrometer

Item number: 468-276

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 0000021605



Description

A water-resistant Mitutoyo bore gauge comprising a digital/analogue display unit and measuring head. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output. A ratchet stop guarantees repeatable measurement.


Features

Inch-Metric:

Inch/Metric

Digital/Analog:	Digital
Range:	6-7" "
Digital step:	0.0001"
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium-coated hardened steel taper: tungsten carbide
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection
Data output:	Yes
Mass:	1120 g

Dimensions



L1: 286.3 - 311.3 mm

L2: 151.4 mm

Accessories

Optional accessories:

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **111.00 €***

Suggested retail price: ~~141.00 €*~~



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type

Art No. 05CZA662

Suggested retail price: **105.00 €***



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type

Art No. 05CZA663

Suggested retail price: **107.00 €***



Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: **62.00 €***



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: 216.00 €*
~~216.00 €~~



Setting Ring 6"

Steel

Art No. 177-301

Suggested retail price: 1,061.00 €*
~~1,061.00 €~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: 129.00 €*
~~187.00 €~~

Suggested retail price: 187.00 €*
~~187.00 €~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: 129.00 €*
~~187.00 €~~

Suggested retail price: 187.00 €*
~~187.00 €~~

Promotion!

Mitutoyo

MiCAT

the standard in world
metrology software
MeasurLink®

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: 268.00 €*
~~340.00 €~~

Suggested retail price: 340.00 €*
~~340.00 €~~



Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €* *incl. VAT