

## Digital 3-Point Internal Micrometer

Item number: 468-280

### Images



Dust- and  
Waterproof  
IP65

[www.tuv.com](http://www.tuv.com)  
ID 0000021605



### Description

A water-resistant Mitutoyo bore gauge comprising a digital/analogue display unit and measuring head. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output. A ratchet stop guarantees repeatable measurement.


### Features

Inch-Metric:

Inch/Metric

|  |  |
|--|--|
| <b>Digital/Analog:</b>                       | Digital  |
| <b>Range:</b>                                | 10-11" "   |
| <b>Digital step:</b>                         | 0.0001"  |
| <b>Power supply:</b>                         | 1 battery SR-44  |
| <b>Battery life:</b>                         | Approx. 1.2 years  |
| <b>Display:</b>                              | LCD, character height 7.5 mm   |
| <b>Measuring face:</b>                       | Titanium-coated hardened steel<br>taper: tungsten carbide                                  |
| <b>ABS / INC (INC ZERO):</b>                 | Yes  |
| <b>Auto Power OFF after 20 min. non use:</b> | Yes  |
| <b>Low voltage alarm:</b>                    | Yes  |
| <b>Function lock:</b>                        | Yes  |
| <b>HOLD:</b>                                 | Yes  |
| <b>2 x PRESET:</b>                           | Yes  |
| <b>Delivered:</b>                            | Including box, hex wrench, spanner, screwdriver, 1 SR44 battery, certificate of inspection |
| <b>Data output:</b>                          | Yes  |
| <b>Mass:</b>                                 | 1480 g   |

#### Dimensions



**L1:** 286.3 - 311.3 mm

**L2:** 151.4 mm

#### Accessories

Optional accessories:



**Micrometer Stand, Adjustable Angle Type**

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

Promo price: **56.00 €\***

~~Suggested retail price: 70.00 €\*~~

Promotion!



## Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **76.00 €\***

Suggested retail price: ~~110.00 €\*~~

Promotion!



## USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **111.00 €\***

Suggested retail price: ~~141.00 €\*~~



## Digimatic Cable with Data Button IP Type

1 m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €\*



## Digimatic Cable with Data Button IP Type

2 m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €\*



## Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: 62.00 €\*



## Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range  
Art No. 952623  
Suggested retail price: 216.00 €\*  

---



## Setting Ring 10"

Steel  
Art No. 177-309  
Suggested retail price: 2,364.00 €\*  

---

Promotion!



## U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: **129.00 €\***   
Suggested retail price: ~~187.00 €\*~~

Promotion!



## U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: **129.00 €\***   
Suggested retail price: ~~187.00 €\*~~

Promotion!

Mitutoyo

**MiCAT**  
the standard in world  
metrology software  
**MeasurLink**

## USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)  
Art No. 06AGR543  
Promo price: **268.00 €\***   
Suggested retail price: ~~340.00 €\*~~

USB-ITPAK

Consumable spares:

---



**Battery SR44 1,5 V**

Art No. 938882

Suggested retail price: 7.00 €\*  

---