

Digital 3-Point Internal Micrometer Set

Item number: 468-977

Images



Description


A water-resistant Mitutoyo bore gauge set comprising a digital/analogue display unit with interchangeable measuring heads, the appropriate setting rings, and an extension tube for deep-measuring applications. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output.

Features

Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Range:	0,5 - 0,8 "

Digital step:	0.001 mm, 0.001 mm/0.00005" (models up to 4") / 0.001 mm/0.0001" (models over 5")
Individual ranges:	0.5-0.65", 0.65-0.8"
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium coated tungsten carbide (6-12 mm) Titanium coated hardened steel (12-200 mm) Taper: tungsten carbide
Setting rings included:	ø0.65" (177-182)
Remarks:	150 mm extension
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner (2 pcs.), screwdriver, 1 SR44 battery, setting ring (1 pcs.), extension rod, certificate of inspection
Data output:	Yes
Mass:	560 g

Dimensions



L1: 197.5 - 201.5 mm

L2: 84 mm

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT
the standard in world metrology software
MeasurLink®

USB-ITPAK

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: 268.00 €*

~~Suggested retail price: 340.00 €*~~



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type
Art No. 05CZA662
Suggested retail price: 105.00 €*



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type
Art No. 05CZA663
Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
Art No. 06AFM380B
Promo price: **111.00 €***
~~Suggested retail price: 141.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Promo price: **129.00 €***
~~Suggested retail price: 187.00 €*~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Promo price: **129.00 €***
~~Suggested retail price: 187.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: **62.00 €***



Holtest, Borematic Extension 150mm

for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: **120.00 €***



Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
