

**Digital 3-Point Internal
Micrometer Set**

Item number: 468-978

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 0000021605



A water-resistant Mitutoyo bore gauge set comprising a digital/analogue display unit with interchangeable measuring heads, the appropriate setting rings, and an extension tube for deep-measuring applications. Suitable for measuring to the bottom of blind holes. Titanium-coated contact faces for enhanced durability. Digimatic data output.

Features

Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Range:	0,275 - 2 "
Digital step:	0.001 mm, 0.001 mm/0.00005" (models up to 4") / 0.001 mm/0.0001" (models over 5")
Individual ranges:	0.8-1", 1-1.2", 1.2-1.6", 1.6-2"
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium coated tungsten carbide (6-12 mm) Titanium coated hardened steel (12-200 mm) Taper: tungsten carbide
Setting rings included:	ø1" (177-184) ø1.6" (177-291)
Remarks:	150 mm extension
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner (2 pcs.), screwdriver, 1 SR44 battery, setting rings (2 pcs.), extension rod, certificate of inspection
Data output:	Yes
Mass:	1170 g

Dimensions

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: **268.00 €***

Suggested retail price: ~~340.00 €*~~



Digimatic Cable with Data Button IP Type



1 m, Micrometer Type

Art No. 05CZA662

Suggested retail price: 105.00 €*

Digimatic Cable with Data Button IP Type



2 m, Micrometer Type

Art No. 05CZA663

Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data
Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **111.00 €***

Suggested retail price: ~~141.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: ~~62.00 €*~~



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range

Art No. 952622

Suggested retail price: ~~136.00 €*~~



Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
