

Digital 3-Point Internal Micrometer Set

Item number: 468-983

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 0000021605



Description


These are three-point internal micrometers that offer you the following benefits:

- Complete unit set.
- Titanium-coated measuring pins give you excellent durability and impact resistance.
- They also have excellent resistance against water and dust (IP65 protection level), allowing you to use this product in machining situations that include splashing coolant fluid.
- Large LCD display with character height of 7.5 mm enables you to read measurements easily.
- With setting rings but without extensions.

Features

Model:	HTD-50RFST
Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	25 - 50 mm
Digital step:	0,001 mm
Individual ranges:	25-30, 30-40, 40-50 mm
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium coated tungsten carbide (6-12 mm) Titanium coated hardened steel (12-100 mm) Taper: tungsten carbide
Models included:	468-167 / 468-168 / 468-169
Setting rings included:	ø30 mm (177-288) ø40 mm (177-290)
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner (2 pcs.), screwdriver, 1 SR44 battery, setting rings (2 pcs.), extension rod, certificate of inspection
Data output:	Yes
Mass:	1480 g

Dimensions



Accessories

Optional accessories:

Promotion!

Mitutoyo

MICAT
the standard in world
metrology software
MeasurLink®



USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: **259.00 €***

Suggested retail price: ~~340.00 €*~~



Digimatic Cable with Data Button IP Type

1m, Micrometer Type

Art No. 05CZA662

Suggested retail price: **105.00 €***



Digimatic Cable with Data Button IP Type

2m, Micrometer Type

Art No. 05CZA663

Suggested retail price: **107.00 €***

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type

Art No. 06AFM380B

Promo price: **109.00 €***

Suggested retail price: ~~141.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type

Art No. 02AZD790B

Promo price: **72.90 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €***

Suggested retail price: ~~70.00 €*~~

Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: **62.00 €***



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range

Art No. 952622

Suggested retail price: **128.00 €***



Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 10.00 €* *incl. VAT