

Digital 3-Point Internal Micrometer Set

Item number: 468-990

Images



Dust- and
Waterproof
IP65

www.tuv.com
ID 0000021605



Description

These are three-point internal micrometers that offer you the following benefits:

- Complete unit set.
- Titanium-coated measuring pins give you excellent durability and impact resistance.
- They also have excellent resistance against water and dust (IP65 protection level), allowing you to use this product in machining situations that include splashing coolant fluid.
- Large LCD display with character height of 7.5 mm enables you to read measurements easily.
- With setting rings but without extensions.


Features

Inch-Metric:

Inch/Metric

Digital/Analog:	Digital
Range:	3 - 4 "
Digital step:	0.001 mm, 0.001 mm/0.00005" (models up to 4") / 0.001 mm/0.0001" (models over 5")
Individual ranges:	3-3.5", 3.5-4"
Power supply:	1 battery SR-44
Battery life:	Approx. 1.2 years
Display:	LCD, character height 7.5 mm
Measuring face:	Titanium coated tungsten carbide (6-12 mm) Titanium coated hardened steel (12-100 mm) Taper: tungsten carbide
Models included:	468-272 / 468-273
Setting rings included:	ø3.5" (177-319)
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Function lock:	Yes
HOLD:	Yes
2 x PRESET:	Yes
Delivered:	Including box, hex wrench, spanner (2 pcs.), screwdriver, 1 SR44 battery, setting ring (1 pcs.), extension rod, certificate of inspection
Data output:	Yes
Mass:	1990 g

Dimensions



L1: 219.6 - 232.6 mm

L2: 105.4 mm

Accessories

Optional accessories:

Promotion!




the standard in world metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: 268.00 €*

Suggested retail price: ~~340.00 €*~~



USB-ITPAK



Digimatic Cable with Data Button IP Type

1 m, Micrometer Type
Art No. 05CZA662
Suggested retail price: 105.00 €*



Digimatic Cable with Data Button IP Type

2 m, Micrometer Type
Art No. 05CZA663
Suggested retail price: 107.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, with Data Button IP Micrometer Type
Art No. 06AFM380B
Promo price: **111.00 €***
Suggested retail price: ~~141.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Promo price: **129.00 €***
Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Promo price: **129.00 €***
Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable B for U-WAVE

with Data Button for IP Micrometer Type
Art No. 02AZD790B

Promo price: **76.00 €***

Suggested retail price: ~~110.00 €*~~

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Holder for Micrometer Stand

for Series 468

Art No. 04AZB157

Suggested retail price: **62.00 €***



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range

Art No. 952623

Suggested retail price: **216.00 €***

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
