

## Dial Caliper

Item number: 505-732

### Images



### Description

A Mitutoyo dial caliper equipped with standard outside and inside jaws. Hardened stainless steel construction with titanium-coated sliding surfaces for low friction/wear.

### Features

|                                      |                       |
|--------------------------------------|-----------------------|
| <b>Range:</b>                        | 0 - 150 mm            |
| <b>Graduation:</b>                   | 0,01 mm<br>1 mm/rev   |
| <b>Delivered:</b>                    | Including plastic box |
| <b>Depth bar:</b>                    | flat                  |
| <b>Max. Permissible Error E MPE:</b> | ±0,02 mm              |
| <b>Max. Permissible Error S MPE:</b> | ±0,04 mm              |
| <b>Mass:</b>                         | 176 g                 |

### Dimensions

### Accessories


Optional accessories:



### **Depth Base Attachment for Caliper**

75mm width for 100, 150, 200mm Range  
Art No. 050083-10  
Suggested retail price: 60.00 €\*  

---



### **Depth Base Attachment for Caliper**

100mm width for 100, 150, 200mm Range  
Art No. 050084-10  
Suggested retail price: 67.00 €\*  

---