

Dial Caliper ID/OD Carbide Tipped Jaws

Item number: 505-748

Images



Description

This inch dial caliper allows you to take reliable measurements and offers you the following benefits:

- Ultra-smooth sliding and high shock protection
- Easy to read dial with large character height

Features

Locking screw:	Yes
Range:	0 - 12 "
Graduation:	0.001" 0.1"/rev
Delivered:	Including plastic box
Depth bar:	flat
Thumb roller:	Yes
Max. Permissible Error E MPE:	±0.002"
Max. Permissible Error S MPE:	±0,0025"
Mass:	370 g

Accessories

Optional accessories:



Depth Base Attachment for Caliper

125mm width for 300mm Range
Art No. 050085-10
Suggested retail price: 74.00 €*

