

2-Point Inside Measuring Instrument

Item number: 511-834

Images



Description

This is a micrometer head that enables measurements without interchangeable anvils. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.
- Wide measuring range with sub-anvils.

Features

Digital/Analog:	Analog
Accuracy:	2 μm
Repeatability:	0,5 μm
Delivered:	In a box with 3 sub-anvils, 2 spanner 301336

Dimensions

a: 9 mm
b: 150 mm
c: 50 mm
d: 16.5 mm
e: 28.9 mm mm
D1: 12.8 mm
D2: 12 mm
R1: SR10
R2: SR1.0

Accessories

Optional accessories:



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",
Flat Back Plate
Art No. 543-312B-10
Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Extension Rod Serie 511

125mm, 12mm Rod Diameter
Art No. 953552
Suggested retail price: 251.00 €*



Extension Rod Serie 511

250mm, 12mm Rod Diameter
Art No. 953553
Suggested retail price: 275.00 €*



Extension Rod Serie 511

500mm, 12mm Rod Diameter
Art No. 953554
Suggested retail price: 493.00 €*

Extension Rod Serie 511

750mm, 12mm Rod Diameter

Art No. 953555

Suggested retail price: 655.00 €*


Extension Rod Serie 511

1000mm, 12mm Rod Diameter

Art No. 953556

Suggested retail price: 907.00 €*


Standard accessories:

Sub Anvil .4"/511

Art No. 208893

Price on application


Sub Anvil .8"/511

Art No. 208895

Price on application


Spanner R=7,3/4,5mm

Micrometer

Art No. 301336

Suggested retail price: 7.00 €*


