

Dial Test Indicator, Horizontal Type

Item number: 513-425-10A

Images



Description

This is a Dial Test Indicator (Lever Type) which offers you the following benefits:

- Drastically enhanced durability, sensitivity and visibility.
- Glare-free flat crystal face allows easy reading of graduations.
- O-ring seal on the bezel has the effect of providing smooth rotation and prevents dust and oil from penetrating through to the dial face.
- The stylus length is on the dial face to reorder a replacement.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	In a box with stem $\varnothing 8/4$ mm, stylus $\varnothing 1/2/3$ mm
Range:	0.6 mm
Graduation:	0.002 mm
MPE any 10 scale divisions:	2 μm
MPE any 1/2 revolution:	3 μm
MPE any 1 revolution:	5 μm
MPE measuring range:	7 μm
H MPE (Hysteresis):	4 μm
R MPE (Repeatability):	1 μm


Carbide stylus tip ø2 mm No.: 103011

Mass: 45 g

Contact point: Thread M 1.7 x 0.35

Remarks: Plus set

Dimensions



L1: 18.7 mm

L2: 15.2 mm

L3: 27.5 mm

D Ø: 40 mm

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

Standard accessories:



Stem for Standard Type Series 513

D=4mm

Art No. 21CAB106

Suggested retail price: 15.00 €*



Stem for Standard Type Series 513

D=8mm

Art No. 21CAB104

Suggested retail price: 15.00 €*



Stylus for Serie 513

D= 1mm, 15,2mm Length, Carbide
Art No. 131314
Suggested retail price: 10.00 €*



Stylus for Serie 513

D= 2mm, 15,2mm Length, Carbide
Art No. 103011
Suggested retail price: 21.00 €*



Stylus for Serie 513

D= 3mm, 15,2mm Length, Carbide
Art No. 131315
Suggested retail price: 12.00 €*



Knurled Clamp Ring for Stem

Lever Indicator Serie 513
Art No. 190322
Suggested retail price: 12.00 €*
