


2-Point Inside Measuring Instrument

Item number: 526-122-20

Images



Description


This is a two point split contact point ideally suited to smaller bore measurements. It offers you the following benefits:

- A precision bore gauge so you can make quick and accurate measurements of small hole diameters (0.95-18 mm).
- You can replace the analogue indicator fitted to this instrument with a customer-supplied Digimatic indicator if you need.
- The contact point is hard chrome coated.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	0.3 - 0.4 "
Graduation:	0.0001 "
Repeatability:	2 μ m
Measuring depth:	2.2"
No. Dial Indicator:	2923AB-10
Number of anvils:	6
Accuracy:	4 μ m 6 μ m for range 0.4-0.7 "
Delivered:	In a box, with dial indicator and cover for dial indicator, without setting ring

Dimensions



Accessories

Optional accessories:



Stand for Bore Gauge Series 526

D=60mm Table, 38mm Table Stroke
Art No. 215-120-10
Suggested retail price: 1,178.00 €*



Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",
Flat Back Plate
Art No. 543-312B-10
Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:



2-Point Inside Measuring Instrument

Bore Gauge for Extra Small Holes, 0,3-0,4",
w/o Indicator
Art No. 526-103
Suggested retail price: 293.00 €*



Dial Gauge, Flat Back, ANSI/AGD Type

Jewelled Bearing, Shockproof, 0,05", 0,0001"
Art No. 2923AB-10
Suggested retail price: 145.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000
Suggested retail price: 20.00 €*
