


Vernier Caliper, Standard Jaws Nib Style

Item number: 533-505

Images



Description

These vernier calipers with nib style and standard jaws let you take easy, metric measurements. They offer you the following benefits:

- You can read inside and outside measurements directly from the upper and lower vernier scales.
- Main scale and vernier scale satin chrome finish gives you high readability.

Features

Delivered:	In a box
Range:	0 - 750 mm
Graduation:	0.02 mm
Inside measuring from:	20.1 mm
Max. Permissible Error E MPE:	$\pm 0,06$ mm
Max. Permissible Error S MPE:	$\pm 0,06$ mm
Mass:	1550 g

Dimensions

