

Vernier Scribing Caliper, Carb. Jaws

Item number: 536-222

Images



Description

Scribe caliper with carbide tipped measuring surfaces and depth gauge

Features

Delivered:	In a paper case
Range:	0 - 200 mm
Graduation:	0,05 mm
Max. Permissible Error E MPE:	$\pm 0,05$ mm
Max. Permissible Error S MPE:	$\pm 0,07$ mm
Mass:	180 g

Dimensions



Accessories


Standard accessories:



Depth Base Attachment for Caliper

75mm width for 100, 150, 200mm Range
Art No. 050083-10
Suggested retail price: 60.00 €*

Depth Base Attachment for Caliper



100mm width for 100, 150, 200mm Range

Art No. 050084-10

Suggested retail price: **67.00 €***
