

Features

| | |
|-------------------------------------|---|
| Model: | AT103-4500 |
| Accuracy: | 100 to 3000 mm (5+5L/1000) μ m 3250 to 6000 mm (5+8L/1000) μ m L = Effective range (mm) |
| Output waveform: | Two 90° phase-shifted sinusoidal signals |
| Max. drive speed: | 50 m/min. |
| Signal period: | 20 μ m |
| Scale reference points: | every 50 mm |
| Dust/water protection level: | IP53 |
| Cable length: | 10 m |
| Effective Length: | 4500 mm |
| Mass: | 13.8 kg |

Accessories

Optional accessories:



Extension Cable 2M

Art No. 09AAA033A
Suggested retail price: 242.00 €*
Photo Not Available

Extension Cable 5M

Art No. 09AAA033B
Suggested retail price: 333.00 €*
Photo Not Available

Extension Cable 7M

Art No. 09AAA033C
Suggested retail price: 384.00 €*
Photo Not Available



Linear Scale Counter KA-212

Art No. 174-183D

Suggested retail price: 650.00 €*



Linear Scale Counter KA-213

Art No. 174-185D

Suggested retail price: 782.00 €*
