



## Features

<b>Model:</b>	AT103-6000
<b>Accuracy:</b>	100 to 3000 mm (5+5L/1000) $\mu$ m 3250 to 6000 mm (5+8L/1000) $\mu$ m L = Effective range (mm)
<b>Output waveform:</b>	Two 90° phased-shifted sinusoidal signals
<b>Max. drive speed:</b>	50 m/min.
<b>Signal period:</b>	20 $\mu$ m
<b>Scale reference points:</b>	50 mm
<b>Dust/water protection level:</b>	IP53
<b>Cable length:</b>	15 m
<b>Effective Length:</b>	6000 mm
<b>Mass:</b>	18.2 kg

## Accessories

### Optional accessories:



#### Extension Cable 2M

Art No. 09AAA033A  
Suggested retail price: 242.00 €\*  
\*



#### Extension Cable 5M

Art No. 09AAA033B  
Suggested retail price: 333.00 €\*  
\*



#### Extension Cable 7M

Art No. 09AAA033C  
Suggested retail price: 384.00 €\*  
\*



## Linear Scale Counter KA-212

Art No. 174-183D

Suggested retail price: 650.00 €\*  

---



## Linear Scale Counter KA-213

Art No. 174-185D

Suggested retail price: 782.00 €\*  

---