


Linear Scale AT113

Item number: 539-208-40

Images



Description

These linear scales are built for limited installation space

- Glass scale - Zero not coded
- Expansion factor $(8 \pm 1) \times 10^{-6}/K^{-1}$
- An armoured inox signal cable is used to connect the DRO counter

Features

Model:	AT113-450F
Accuracy:	High-accuracy type (3+3L/1000) μm L = Effective range (mm)
Output waveform:	Two 90° phase-shifted sinusoidal signals
Max. drive speed:	120 m/min
Signal period:	20 μm
Scale reference points:	50 mm
Dust/water protection level:	IP53
Cable length:	3.5 m
Effective Length:	450 mm

Mass:

1.14 kg

Accessories

Optional accessories:



Extension Cable 2M

Art No. 09AAA033A

Suggested retail price: 242.00 €*



Extension Cable 5M

Art No. 09AAA033B

Suggested retail price: 333.00 €*



Extension Cable 7M

Art No. 09AAA033C

Suggested retail price: 384.00 €*



Linear Scale Counter KA-212

Art No. 174-183D

Suggested retail price: 650.00 €*



Linear Scale Counter KA-213

Art No. 174-185D

Suggested retail price: 782.00 €*
