

Digital Indicator ID-N, IP66, ANSI/AGD

Item number: 543-571

Images



Safety
Dust- and
Water-
Protected

www.tuv.com
ID 0000007161

ABSOLUTE®

IP66

Description

A Mitutoyo slim-style dustproof and waterproof digital indicator suitable for use in the presence of coolant or cutting oil. ABSOLUTE System scale for error free, high-speed measurement. Functionality includes switchable resolution, tolerance judgement, data hold and readout rotation. SPC data output.

Features

Model:	ID-N1012E
Digital/Analog:	Digital
Inch-Metric:	Inch/Metric
Functions:	ANSI/AGD type
Range:	0.5"/12.7 mm

Optional accessories:



Spindle Lifting Knob

for 0,5", ANSI/AGD Type
Art No. 21EZA150
Suggested retail price: 37.00 €*
*



U-WAVE fit Transmitter Mounting Plate

for ID-N Digital Indicator
Art No. 02AZF675
Suggested retail price: 45.00 €*
*



Back Plate with Center Lug AGD Type

for ID-N/ID-B Indicator
Art No. 21EZA146
Suggested retail price: 25.50 €*
*



Connection Cable G for U- WAVE

for IP66 Indicators ID-N and ID-B
Art No. 02AZD790G
Suggested retail price: 105.00 €*
*



U-WAVE fit, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-622
Suggested retail price: 185.00 €*
*



U-WAVE fit, Buzzer Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-623
Suggested retail price: 185.00 €*



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight
for ID-N/ID-B
Art No. 06AFM380G
Suggested retail price: 124.00 €*



Silicon rubber boot for ID-C, ID-N, ID-S

Art No. 238774
Price on application



Digimatic Cable for ID-N/ ID-B 1m

Art No. 21EAA194
Suggested retail price: 66.00 €*



Digimatic Cable for ID-N/ ID-B 2m

Art No. 21EAA190
Suggested retail price: 76.00 €*



Digimatic Cable for External Preset/Zero

1 m, ID-N/ID-B Indicator
Art No. 21EAA210
Suggested retail price: 191.00 €*



Digimatic Cable for External Preset/Zero

2 m, ID-N/ID-B Indicator
Art No. 21EAA211
Suggested retail price: 217.00 €*



USB Input Tool Interface Box

Digimatic/Digimatic 2/Digimatic S1 Interface
Art No. 264-020
Suggested retail price: 259.00 €*



U-WAVE-T, IP67 Type

Wireless Transmitter
Art No. 02AZD730G
Suggested retail price: 187.00 €*



U-WAVE-T, Buzzer Type

Wireless Transmitter
Art No. 02AZD880G
Suggested retail price: 187.00 €*



U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-626
Suggested retail price: 185.00 €*



U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for
Micrometer/Indicator
Art No. 264-627
Suggested retail price: 185.00 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch
Art No. 21BZB005
Suggested retail price: 13.30 €*



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*

NBR Rubber Boot

Digital Gauge Series 543

Art No. 21EAA423

Suggested retail price: 2.20 €*

