


Digital ABS Carb. Fibre Caliper Long Jaw

Item number: 552-150-10

Images



Description

This is a lightweight standard model of Digimatic caliper with extra-long jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

Features

Model:	CFC-45GL
DATA (output with cable) / HOLD (display value):	Yes
Range:	0 - 450 mm
Inside measuring from:	20.1 mm
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0,06 mm
Max. Permissible Error S MPE:	±0,06 mm
Max. response speed:	Unlimited
ORIGIN (ABS-Zero):	Yes
OFFSET:	20 mm
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
Data output:	Yes
Battery life:	Approx. 5000 hours
Mass:	1215 g

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Suggested retail price: 340.00 €*

A placeholder image for the USB-ITPAK product, consisting of a red rectangular area on top and a light beige rectangular area on the bottom. The text "USB-ITPAK" is centered in the red area.

USB-ITPAK

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
