

## Digital ABS Carb. Fibre Caliper Ceramic

Item number: 552-156-10

### Images



Safety  
Dust- and  
Water-  
Protected

www.tuv.com  
ID 0000022582

# ABSOLUTE®

# IP66

### Description

This is a lightweight standard model of Digimatic caliper with ceramic jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

### Features

<b>Model:</b>	CFC-60GC
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>Delivered:</b>	In a box with SR44 battery
<b>Range:</b>	0 - 600 mm
<b>Inside measuring from:</b>	20.1 mm
<b>Max. Permissible Error E MPE:</b>	±0,04 mm
<b>Max. Permissible Error S MPE:</b>	±0,04 mm
<b>OFFSET:</b>	20 mm
<b>Max. response speed:</b>	Unlimited
<b>ORIGIN (ABS-Zero):</b>	Yes





### Inside Groove Jaws Series 552

2 pcs., Metric  
Art No. 914057  
Suggested retail price: 312.00 €\*  

---

#### Spare parts

##### Consumable spares:

---



### Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: 10.00 €\*  

---