

Digital ABS Carb. Fibre Caliper Long Jaw

Item number: 552-164-10

Images



Description

This is a lightweight standard model of Digimatic caliper with extra-long jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

Features

| | |
|---|----------------------------|
| Model: | CFC-80"GL |
| DATA (output with cable) / HOLD (display value): | Yes |
| Range: | 0 - 80 " |
| Inside measuring from: | 25.5 mm/1004" |
| Delivered: | In a box with SR44 battery |
| Max. Permissible Error E MPE: | ±0,0055" |
| Max. Permissible Error S MPE: | ±0,0055" |
| Max. response speed: | Unlimited |
| ORIGIN (ABS-Zero): | Yes |
| OFFSET: | 0.5" |
| Auto Power OFF after 20 min. non use: | Yes |
| Low voltage alarm: | Yes |
| Data output: | Yes |
| Battery life: | Approx. 5000 hours |
| Mass: | 2890 g |

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Suggested retail price: 340.00 €*

A placeholder image for the USB-ITPAK product, consisting of a red rectangular area on top and a light beige rectangular area on the bottom. The text "USB-ITPAK" is centered in the red area.

USB-ITPAK

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
