

Digital ABS Carbon Fibre Caliper

Item number: 552-303-10

Images



Safety
Dust- and
Water-
Protected

www.tuv.com
ID 000022582

ABSOLUTE®

IP66

Description

This is a lightweight standard model of Digimatic caliper with steel jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

Features

Model:	CFC-60G
DATA (output with cable) / HOLD (display value):	Yes
Range:	0 - 600 mm
Inside measuring from:	20.1 mm
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0,04 mm
Max. Permissible Error S MPE:	±0,04 mm
Max. response speed:	Unlimited
ORIGIN (ABS-Zero):	Yes
Low voltage alarm:	Yes
Data output:	Yes

Battery life: Approx. 5000 hours

Mass: 790 g

Dimensions

Accessories

Optional accessories:

Mitutoyo

MiCAT

the standard in world
metrology software
measurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Suggested retail price: **340.00 €***

USB-ITPAK



Holders (Clamps) Series 552

2 pcs., 450 and 600mm Range

Art No. 914053

Suggested retail price: **209.00 €***



Center to Center Jaws Series 552

2 pcs., (≥10,1mm) Metric

Art No. 914055

Suggested retail price: **272.00 €***



Inside Groove Jaws Series 552

2 pcs., Metric

Art No. 914057

Suggested retail price: **312.00 €***

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
