

Digital ABS Carbon Fibre Caliper

Item number: 552-304-10

Images



Safety
Dust- and
Water-
Protected

www.tuv.com
ID 000022582

ABSOLUTE®

IP66

Description

This is a lightweight standard model of Digimatic caliper with steel jaws.

It offers you the following benefits:

- Its ultra-lightweight design (with carbon fibre reinforced material) reduces total weight by up to 50%.
- It has excellent resistance against water and dust (IP66 protection level) enabling you to use it in machining situations that include splashing coolant fluid.
- Direct readout of inside measurements from the LCD (you can easily set the offset value by using the offset button).
- Preset function lets you set a desired starting point.

Features

Model:	CFC-100G
DATA (output with cable) / HOLD (display value):	Yes
Delivered:	In a box with SR44 battery
Range:	0 - 1,000 mm
Inside measuring from:	20.1 mm

Max. Permissible Error E MPE: ±0,05 mm

Max. Permissible Error S MPE: ±0,05 mm

Max. response speed: Unlimited

ORIGIN (ABS-Zero): Yes

Low voltage alarm: Yes

Data output: Yes

Battery life: Approx. 5000 hours

Mass: 1760 g

Dimensions

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: **259.00 €***

Suggested retail price: ~~340.00 €*~~

USB-ITPAK



Holders (Clamps) Series 552

2 pcs., >600mm Range

Art No. 914054

Suggested retail price: **214.00 €***



Center to Center Jaws Series 552

2 pcs., (≥10,1mm) Metric

Art No. 914055

Suggested retail price: **272.00 €***



Inside Groove Jaws Series 552

2 pcs., Metric
Art No. 914057
Suggested retail price: 312.00 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 10.00 €*
