

Digital ABS Carbon Fibre Caliper

Item number: 552-312-10

Images



Description

A Mitutoyo waterproof digital caliper suitable for use in the presence of coolant or cutting oil. Lightweight, carbon-fibre construction for easy handling and equipped with plain stainless-steel jaws. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.

Features

Model:	CFC-18"G
DATA (output with cable) / HOLD (display value):	Yes
Range:	0 - 18 "
Inside measuring from:	12.8mm/0.504"
Delivered:	In a box with SR44 battery
Max. Permissible Error E MPE:	±0.002"
Max. Permissible Error S MPE:	±0.002"
Max. response speed:	Unlimited
ORIGIN (ABS-Zero):	Yes
Low voltage alarm:	Yes
Data output:	Yes
Battery life:	Approx. 5000 hours
Mass:	715 g

Dimensions

Accessories

Optional accessories:

Mitutoyo

MiCAT
the standard in world
metrology software
MeasurLink

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Suggested retail price: 340.00 €*


USB-ITPAK



Holders (Clamps) Series 552

2 pcs., 450 and 600mm Range

Art No. 914053

Suggested retail price: 209.00 €*


Center to Center Jaws Series 552

2 pcs., (≥10,26mm) Inch


Art No. 914056

Suggested retail price: 272.00 €*


Measuring Jaw

2 pcs., (≥50,9mm) Inch

Art No. 914058

Suggested retail price: 312.00 €*


Standard accessories:



Holders (Clamps) Series 552

2 pcs., 450 and 600mm Range
Art No. 914053
Suggested retail price: 209.00 €*



Center to Center Jaws Series 552

2 pcs., ($\geq 10,1$ mm) Metric
Art No. 914055
Suggested retail price: 272.00 €*



Inside Groove Jaws Series 552

2 pcs., Metric
Art No. 914057
Suggested retail price: 312.00 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*