

## Digital ABS Borematic (Internal) Set

Item number: 568-926-10

### Images



# ABSOLUTE®



### Description

This is a Three-Point Digimatic Snap Open Bore Gauge Set with one display unit and interchangeable heads.

It offers you the following benefits:

- It enables you to take measurements easily and quickly.
- Titanium-coated measuring pins gives you excellent durability and impact resistance.
- 330° rotatable display unit also gives you easy reading at any angle.
- GO/NG tolerance judgement function.

### Features

<b>Model:</b>	SBM-50DST
<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Digital
<b>Range:</b>	25 - 50 mm
<b>Digital step:</b>	0,001 mm
<b>Individual ranges:</b>	25-30 mm 30-40 mm 40-50 mm
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 5000 hours
<b>Display:</b>	LCD, character height: 11 mm
<b>Measuring face:</b>	Titanium coated hardened steel taper: tungsten carbide

<b>Measuring method:</b>	3-point
<b>Setting rings included:</b>	Ø30 mm (177-288) Ø40 mm (177-290)
<b>ABS / INC (INC ZERO):</b>	Yes
<b>ON/OFF:</b>	Yes
<b>Function lock:</b>	Yes
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>GO/±NG judgement:</b>	Yes
<b>Delivered:</b>	In a box with SR44 battery, spanner 04GAA858 (2 pcs.), setting rings (2 pcs.)
<b>Data output:</b>	Yes
<b>Mass:</b>	930 g

## Accessories

### Optional accessories:

**Promotion!**

**Mitutoyo**

**MiCAT**  
the standard in world  
metrology software  
**MeasurLink**


**USB-ITPAK Vers. 3.0**

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

**Promo price: 268.00 €\***

Suggested retail price: ~~340.00 €\*~~



## Spare parts

### Consumable spares:



### Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: 7.00 €\*