

Digital ABS Borematic (Internal) Set

Item number: 568-929-10

Images



ABSOLUTE®



Description

This is a Three-Point Digimatic Snap Open Bore Gauge Set with one display unit and interchangeable heads.

It offers you the following benefits:

- It enables you to take measurements easily and quickly.
- Titanium-coated measuring pins gives you excellent durability and impact resistance.
- 330° rotatable display unit also gives you easy reading at any angle.
- GO/NG tolerance judgement function.

Features



Model:	SBM-1"DST
Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Range:	0,5 - 1 "
Digital step:	0,00005" / 0,001 mm
Individual ranges:	0.5-0.65" 0.65-0.8" 0.8-1"
Power supply:	1 battery SR-44
Battery life:	Approx. 5000 hours
Display:	LCD, character height: 11 mm
Measuring face:	Titanium coated hardened steel taper: tungsten carbide

Measuring method:	3-point
Setting rings included:	Ø0.65" (177-182) Ø0.8" (177-287)
ABS / INC (INC ZERO):	Yes
ON/OFF:	Yes
Function lock:	Yes
DATA (output with cable) / HOLD (display value):	Yes
2 x PRESET:	Yes
GO/±NG judgement:	Yes
Delivered:	In a box with SR44 battery, spanner 04GAA858 (2 pcs.), setting rings (2 pcs.)
Data output:	Yes
Mass:	690 g


Accessories

Optional accessories:

Promotion!

the standard in world
metrology software




USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available Online)

Art No. 06AGR543

Promo price: 268.00 €*

Suggested retail price: ~~340.00 €*~~



USB-ITPAK

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 7.00 €*