

Digital ABS Borematic (Internal) Set

Item number: 568-956

Images



ABSOLUTE®



Description

This is a Three-Point Digimatic Snap Open Bore Gauge Set with a display unit for each measuring head.

It offers you the following benefits:

- It enables you to take measurements easily and quickly.
- Titanium-coated measuring pins gives you excellent durability and impact resistance.
- 330° rotatable display unit also gives you easy reading at any angle.
- GO/NG tolerance judgement function.

Features

Model:	SBM-25CXFST
Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	12 - 25 mm
Digital step:	0,001 mm
Individual ranges:	12-16 mm 16-20 mm 20-25 mm
Display:	LCD, character height: 11 mm
Measuring face:	Titanium coated hardened steel taper: tungsten carbide

Measuring method:	3-point
Setting rings included:	Ø16 mm (177-177) Ø20 mm (177-286)
Power supply:	1 battery SR-44
Battery life:	approx. 5000 hours
ABS / INC (INC ZERO):	Yes
ON/OFF:	Yes
Function lock:	Yes
DATA (output with cable) / HOLD (display value):	Yes
2 x PRESET:	Yes
Delivered:	In a box with SR44 battery, spanner 04GAA858 (2 pcs.), setting rings (2 pcs.)
Data output:	Yes
GO/±NG judgement:	Yes
Mass:	1520 g

Accessories

Optional accessories:



Digimatic Cable, Flat Straight Type

1m
Art No. 905338
Suggested retail price: 37.00 €*



Digimatic Cable, Flat Straight Type

2m
Art No. 905409
Suggested retail price: 44.00 €*

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type
Art No. 06AFM380F
Promo price: **98.90 €***
Suggested retail price: 124.00 €*

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable F for U-WAVE

Straight, without Data Button

Art No. 02AZD790F

Promo price: **63.90 €***

Suggested retail price: ~~98.00 €*~~

Holtest, Borematic Extension 100mm



for 6-12mm Measuring Range

Art No. 952322

Suggested retail price: **118.00 €***

Holtest, Borematic Extension 150mm



for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: **118.00 €***



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range
Art No. 952622
Suggested retail price: 128.00 €*



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: 222.00 €*

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882
Suggested retail price: 10.00 €*
