

## Digital ABS Borematic (Internal) Set

Item number: 568-968-10

### Images



# ABSOLUTE®



### Description

This is a Three-Point Digimatic Snap Open Bore Gauge Set with a display unit for each measuring head.

It offers you the following benefits:

- It enables you to take measurements easily and quickly.
- Titanium-coated measuring pins gives you excellent durability and impact resistance.
- 330° rotatable display unit also gives you easy reading at any angle.
- GO/NG tolerance judgement function.

### Features

<b>Model:</b>	SBM-3"DFST
<b>Inch-Metric:</b>	Inch/Metric
<b>Digital/Analog:</b>	Digital
<b>Range:</b>	2 - 3 "
<b>Digital step:</b>	0,00005" / 0,001 mm
<b>Individual ranges:</b>	2-2.5" 2.5-3"
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	approx. 5000 hours
<b>Display:</b>	LCD, character height: 11 mm
<b>Measuring face:</b>	Titanium coated hardened steel taper: tungsten carbide

<b>Measuring method:</b>	3-point
<b>Setting rings included:</b>	Ø2.5" (177-315)
<b>ABS / INC (INC ZERO):</b>	Yes
<b>ON/OFF:</b>	Yes
<b>Function lock:</b>	Yes
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>2 x PRESET:</b>	Yes
<b>GO/±NG judgement:</b>	Yes
<b>Delivered:</b>	In a box with SR44 battery, spanner 04GAA858 (2 pcs.), setting ring (1 pcs.)
<b>Data output:</b>	Yes
<b>Mass:</b>	1490 g

## Accessories

### Optional accessories:



### Digimatic Cable, Flat Straight Type

1 m  
Art No. 905338  
Suggested retail price: 37.00 €\*



### Digimatic Cable, Flat Straight Type

2 m  
Art No. 905409  
Suggested retail price: 44.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type  
Art No. 06AFM380F  
Promo price: **98.00 €\***   
Suggested retail price: 124.00 €\*

Promotion!



### U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!



### U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €\***

Suggested retail price: ~~187.00 €\*~~

Promotion!



### Connection Cable F for U-WAVE

Straight, without Data Button

Art No. 02AZD790F

Promo price: **68.00 €\***

Suggested retail price: ~~98.00 €\*~~

### Holtest, Borematic Extension 100mm



for 6-12mm Measuring Range

Art No. 952322

Suggested retail price: **128.00 €\***

### Holtest, Borematic Extension 150mm



for 12-20mm Measuring Range

Art No. 952621

Suggested retail price: **120.00 €\***



### Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range  
Art No. 952622  
Suggested retail price: 136.00 €\*



### Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range  
Art No. 952623  
Suggested retail price: 216.00 €\*

#### Spare parts

Consumable spares:



### Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: 7.00 €\*