

Digital ABS Depth Gauge, Inch/Metric

Item number: 571-215-10

Images




Description

A Mitutoyo digital depth gauge with a 9.8" base. Hardened stainless steel construction. ABSOLUTE System scale for error free, high-speed measurement. SPC data output.

Features

Model:	VDS-24"DC
Inch-Metric:	Inch/Metric
Digital/Analog:	Digital
Power supply:	1 battery SR-44
Range:	0 - 24 "
Digital step:	0.005"/0.01 mm
Max. response speed:	Unlimited
Battery life:	Approx. 20000 hours
Display:	LCD, character height 9 mm (150/200/300 mm), 10 mm (>300 mm)
Base (W x T):	9.8" x 0.39"
ORIGIN (ABS-Zero):	Yes
ON/OFF:	Yes
Low voltage alarm:	Yes
Data output:	Yes
ABS / INC (INC ZERO):	Yes
Mass:	1400 g
Delivered:	In a box with SR44 battery

Dimensions



L: 785 mm

Accessories

Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world
metrology software
MeasurLink®

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: **268.00 €***

Suggested retail price: ~~340.00 €*~~



Digimatic Cable, Straight, Data Button,

1 m

Art No. 959149

Suggested retail price: **48.00 €***



Digimatic Cable, Straight, Data Button

2 m

Art No. 959150

Suggested retail price: **57.00 €***

Promotion!



USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Straight,
with Data Button

Art No. 06AFM380C

Promo price: **98.00 €***

Suggested retail price: ~~124.00 €*~~

Promotion!



U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~



Data Hold Unit

for Digital Caliper

Art No. 959143

Suggested retail price: **39.50 €***

Promotion!



Connection Cable C for U-WAVE

Straight, with Data Button

Art No. 02AZD790C

Promo price: **72.00 €***

Suggested retail price: ~~105.00 €*~~

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*
