

Steel Individual Inch Gauge Block 0.132"

Item number: 614172

Images



Mitutoyo Certificate number: TMS020000 page 1 of 1


CERTIFICATE OF INSPECTION

Instrument: Gauge Block
Grade: G (G10)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06280	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: 68 ± 1.0°F (20 ± 1.0°C)
 BASE OF TEST: 6062 ALUMINUM
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: 0.000010 in/in/°F (0.000018 in/in/°C) (0.000010 in/in/°C) (0.000018 in/in/°C)
 EXTENDED UNCERTAINTY: ± 0.000010 in/in (± 0.000018 in/in) (± 0.000010 in/in) (± 0.000018 in/in)
 PER GAUGE DEPARTMENT: 10.2 x 1.1 / 1.30 in/in (10.2 x 1.1 / 1.30 in/in)
 QUALITY SYSTEM: ISO 9001 Registered Firm - GB, MICHIGAN
 TRACEABILITY: Reported in NIST No. 800-20000-02 (2000) (National Institute of Standards and Technology)

Date: 18th May, 2006


F-0110
 0.132 inch
 0.132 inch
 0.132 inch

