

60HRC Rockwell Hardness Reference Material

Item number: 63ASTM001

Images



Description

Optionally available on request: • calibration of up 3 test scales on one test block • lasered grid for accurate indentation spacing

Features

Description:	Optionally available on request: <ul style="list-style-type: none">■ calibration of up 3 test scales on one test block■ lasered grid for accurate indentation spacing
Method:	Rockwell
Material:	steel
Hardness Value:	60
Scale 1:	HRC
Indenter:	Diamond cone
Preliminary Test Force N:	98.07
Standard:	ASTM E18
Preliminary Test Force kgf:	10
Test Force N:	1471
Test Force kgf:	150
Accreditation body:	DAkKS
Accreditation standard:	ISO 17025
Dimension:	60x60x16mm
Surface:	3.600 mm ²
Net weight:	450 g
Gross weight:	560 g
Product line:	<ul style="list-style-type: none">■ HR-110MR■ HR-210MR■ HR-320MS

- HR-430MR
 - HR-430MS
 - HR-530
 - HR-610
 - HR-620
-