

30HRC Rockwell Hardness Reference Material

Item number: 63ASTM034G

Images



Description

Optionally available on request: • calibration of up 3 test scales on one test block

Features

Description:	Optionally available on request: ■ calibration of up 3 test scales on one test block
Method:	Rockwell
Material:	steel
Hardness Value:	30
Scale 1:	HRC
Indenter:	Diamond cone
Preliminary Test Force N:	98.07
Standard:	ASTM E18
Preliminary Test Force kgf:	10
Test Force N:	980.7
Test Force kgf:	150
Accreditation body:	DAkKS
Accreditation standard:	ISO 17025
Grid:	yes

Dimension:	60x60x16mm
-------------------	------------

Surface:	3.600 mm ²
-----------------	-----------------------

Net weight:	450 g
--------------------	-------

Gross weight:	560 g
----------------------	-------

Product line:	<ul style="list-style-type: none">■ HR-110MR■ HR-210MR■ HR-320MS■ HR-430MR■ HR-430MS■ HR-530■ HR-610■ HR-620
----------------------	---
