

## 40HRC Rockwell Hardness Reference Material

Item number: 63ASTM036G

### Images



### Description

Optionally available on request: • calibration of up 3 test scales on one test block

### Features

<b>Description:</b>	Optionally available on request: ■ calibration of up 3 test scales on one test block
<b>Method:</b>	Rockwell
<b>Material:</b>	steel
<b>Hardness Value:</b>	40
<b>Scale 1:</b>	HRC
<b>Indenter:</b>	Diamond cone
<b>Preliminary Test Force N:</b>	98.07
<b>Standard:</b>	ASTM E18
<b>Preliminary Test Force kgf:</b>	10
<b>Test Force N:</b>	1471
<b>Test Force kgf:</b>	150
<b>Accreditation body:</b>	DAkKS
<b>Accreditation standard:</b>	ISO 17025
<b>Grid:</b>	yes

---

<b>Dimension:</b>	60x60x16mm
-------------------	------------

---

<b>Surface:</b>	3.600 mm <sup>2</sup>
-----------------	-----------------------

---

<b>Net weight:</b>	450 g
--------------------	-------

---

<b>Gross weight:</b>	560 g
----------------------	-------

---

<b>Product line:</b>	<ul style="list-style-type: none"><li>■ HR-110MR</li><li>■ HR-210MR</li><li>■ HR-320MS</li><li>■ HR-430MR</li><li>■ HR-430MS</li><li>■ HR-530</li><li>■ HR-610</li><li>■ HR-620</li></ul>
----------------------	---

---