

Dial Indicator Depth Gauge

Item number: 7218A

Images



Description

This rectangular base dial indicator depth gauge offers you the following benefits:

- It has a hardened, precision ground and micro-lapped reference face on its base.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Graduation:	0.001"
Range:	0 - 8 "
Accuracy:	±0.002"
Stroke:	1" mm
Base flatness:	5 μm
Probe tip:	Ball, R = 1.5 mm (No. 21JZA242)
Extension rods:	1, 2, 4"
Mass:	320 g
Functions:	With indicator No. 2904AB
Delivered:	In a box without spindle lifting lever, with carbide tipped ball point contact element (21JZA242), extension rods (3 pcs.)

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application