

HH-333 Durometer Type D Long/Analogue

Item number: 811-333-10

Images



Description

These compact digital/dial durometers in the Shore D scale can test a range of different materials and offer you the following benefits:

- You can use them for testing the hardness of the materials including hard rubber, hard plastics, acrylic glass, Polystyrene, rigid thermoplastics, vinyl, cellulose acetate, etc.

Features

Model:	HH-333
Model:	HH-333
Display:	Analog Dial
Indenter b:	ø 1,25 mm
Indenter r:	R 0,1 mm
θ:	30°
Pressure foot a:	ø 3 mm
Pressure foot f:	ø 18 mm
Indenter protrusion:	2,5 mm
Spring force WE, WA, WD:	WD=444,5H D [mN]
Dimensions (WxDxH):	188 x 68 x 35 mm
Mass:	0.32 kg
Connector cable for:	HH-300 Series
PIN:	Flat
USB-ITN:	06AFM380F
DP-1VA (264-505):	959149
IT-016U 264-016-10 Hardmatic table:	937387

Accessories

Optional accessories:



Testing stand

HH-300 Series Shore D all types

Art No. 811-012

Suggested retail price: 2,095.00 €*



Testing stand

HH-300 Series Shore A compact types

Art No. 811-013

Suggested retail price: 2,095.00 €*



Testing stand

HH-300 Series Shore A long types

Art No. 811-019

Suggested retail price: 2,095.00 €*



Digimatic Mini Processor DP-1VR

Art No. 264-504

Price on application



Digimatic Cable, Flat Straight Type

1 m

Art No. 905338

Suggested retail price: 37.00 €*



Statistic Processing Printer DP-1VR

CEE Type

Art No. 264-504-5D

Suggested retail price: 463.00 €*



35, 60, 85 Shore D Shore Hardness Reference Material Set

Art No. 218000DMIT

Suggested retail price: 287.00 €*
