

## Shore Durometer

Item number: 811-336-11

### Images



### Description

These compact digital/dial durometers in the Shore A scale can test a range of different materials and offer you the following benefits:

- You can use them for testing the hardness of the materials including soft rubber, elastomers, natural rubber, casting resin, neoprene, polyesters, soft PVC, leather, etc.

### Features

<b>Model:</b>	HH-336-01
<b>Model:</b>	HH-336-01
<b>Shore Scale:</b>	Shore A
<b>Display:</b>	Digital
<b>Indenter b:</b>	ø 1,25 mm
<b>Indenter d:</b>	ø 0,79 mm
<b>θ:</b>	35°
<b>Pressure foot a:</b>	ø 3 mm
<b>Pressure foot f:</b>	ø 18 mm
<b>Indenter protrusion:</b>	2,5 mm
<b>Spring force WE, WA, WD:</b>	WA=550+75 HA [mN]
<b>Dimensions (WxDxH):</b>	151x60x28.5 mm
<b>Mass:</b>	0.26 kg
<b>Connector cable for:</b>	HH-300 Series
<b>PIN:</b>	Flat
<b>U-WAVE-T:</b>	02AZD790F
<b>USB-ITN:</b>	06AFM380F
<b>DP-1VA (264-505):</b>	959149
<b>IT-016U 264-016-10 Hardmatic table:</b>	937387

### Accessories



## Testing stand

HH-300 Series Shore A long types  
Art No. 811-019  
Suggested retail price: 2,095.00 €\*



## 35, 60, 90 Shore A Shore Hardness Reference Material Set

Art No. 218000MIT  
Suggested retail price: 216.00 €\*



## Statistic Processing Printer DP-1VR

CEE Type  
Art No. 264-504-5D  
Suggested retail price: 463.00 €\*



## Digimatic Cable, Flat Straight Type

1m  
Art No. 905338  
Suggested retail price: 37.00 €\*



## Testing stand

HH-300 Series Shore A compact types  
Art No. 811-013  
Suggested retail price: 2,095.00 €\*

