

Granite Surface Plate, DIN 876

Item number: 901-103

Images




Description

- Surface diamond lapped, side face fine ground, backside fine sawn.
- The optional stand is a welded construction including 3 or 5-point bearings and two adjusting screws.
- Delivered with a certificate of inspection

Features

Vickers hardness:	HV 850-900
Flexural strength:	13-22 N/mm ²
Compressive strength:	Approx. 280 N/mm ²
Linear coefficient of expansion:	$(5 - 7.5) \times 10^{-6} \times K^{-1}$
Dimensions L x W x H:	630 x 400 x 70 mm
Accuracy:	DIN 876 grade 2
Max. workpiece load:	130 kg
Delivered:	With steel ball inserts and certificate of inspection
Mass:	53 kg

Dimensions



Accessories

Optional accessories:



Stand (Angle Steel), Granite Plate

630x400x50mm

Art No. 901-931

Suggested retail price: 507.00 €*
